

PRODUCT

Integrity Non-woven Polyester/Cellulose Wipe

TECHNICAL DATASHEET



DESCRIPTION

The Non-woven Polyester/Cellulose wipe is low linting, highly absorbent and durable making it a highly effective general purpose wipe. Ideal for the following applications: laboratories, aerospace, defence electronics, semiconductor, pharmaceutical and biomedical device manufacturing.

FEATURES

- ISO 5-8
- 45% polyester and 55% cellulose
- Highly absorbent and durable
- Available sterile by gamma irradiation

PRODUCT CODE	DESCRIPTION	STERILITY	SIZE (INCH)	QUANTITY (PER PACK)
600-0501	Non-woven Polyester/Cellulose Wipe	Non-Sterile	9 x 9	100
600-0510	Non-woven Polyester/Cellulose Wipe	Non-Sterile	9 x 9	300
600-0520	Non-woven Polyester/Cellulose Wipe	Non-Sterile	12 x 12	100
600-0530	Non-woven Polyester/Cellulose Wipe	Sterile	12 x 12	100
600-0550	Non-woven Polyester/Cellulose Wipe	Non-Sterile	16 x 15	100

To request a quotation or for more information, please call **+44 (0)1473 836205**
email info@integritycleanroom.co.uk or visit www.integritycleanroom.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © 2024 Integrity Cleanroom.

PROPERTIES

SPECIFICATIONS (IN DRY STATE)	VALUE	TEST METHOD
Basis weight	68 g/m ²	
Thickness	0.27 - 0.34 mm	
Absorbency		
Capacity Rate	≤ 250 ml/m ² <1 sec	IEST-RP-CC004.3, Sec 8.1 IEEST-RP-CC004.3, Sec 8.2
Particle Counts		
Particle data representative of a 9" x 9" wipe		
APC ≥ 0.5 µm	200 counts/pc	IEST-RP-CC003.2 (Helmke drum @10rpm)
LPC ≥ 0.5 µm	75 x 10 ⁶ counts/m ²	IEST-RP-CC004.3, Sec 6.1.4
Fibre > 100 µm	86,181 counts/m ²	IEST-RP-CC004.3, Sec 6.1.4, 6.2.2.1, 6.2.2.2
Non Volatile Residue (NVR)		
DI Water IPA	0.021 g/m ² 0.007 g/m ²	IEST-RP-CC004.3, Sec 7.2.1
IONS		
No silicone oil, Amide, DOP detected		
Sodium (Na) Potassium (K) Calcium (Ca) Magnesium (Mg) Chloride (Cl)	33.89 ppm 7.051 ppm 17.37 ppm 4.63 ppm 68.79 ppm	IEST-RP-CC004.3, Sec 7.2.2

To request a quotation or for more information, please call **+44 (0)1473 836205**
 email info@integritycleanroom.co.uk or visit www.integritycleanroom.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © 2024 Integrity Cleanroom.